

HHOG II EPD-Enhanced Bubblers

Safety Bubbler with enhanced EPDv2 explosion prevention.
Due to High Volume Demand, Units now ship Unpainted (Black).



Removable Base



Hydroxy Disbursement Screen



Refill Stopper Pull Chain



EPDv2 Protection

We have updated the design of the original HHOG II EPD-Enhanced Bubbler. With an EPD-Enhanced Bubbler a flashback arrestor is generally not needed. The EPDv2 keeps the bubbler from being destroyed by a flashback, which makes it great for high output Hydroxy Generators!

The bubbler is designed to take a flashback, and safely disburse the explosion out the top through the HHOG II EPDv2's blast ports. A bubbler is necessary to help remove electrolyte condensate and moisture from the Hydroxy gas and protect you from a flashback.

We have 4 sizes available: A 16-inch length, and an 12-inch length. Both come in 2-inch diameter, and 3-inch diameter tube sizes.

FEATURES:

- **Full color instructions:** <http://www.hhoglabs.com/images/HHOG2EPDBubbler.pdf>
 - Unique Automatically Resetting "Blast Relief"
- The attached EPD boasts fully USER SERVICEABLE PARTS. Each internal/external part of the EPD is replaceable!
 - ABS top and bottom reducing junctions for added strength.
 - Output barb has built-in check valve.
 - Easy refill through the EPDv2 means no pesky refill ports, lost lids or seals.
 - "Daisy-Chain-Reaction" resistant screen keeps bubbles scattered and smaller!

Shipping Weight:
Approx. 18 oz each

Content Property of HHOG Labs 2008
All Rights Reserved.

HHOG Labs SRS Ratings:
2X12 model:OD5 3X12 model:OD12
2X16 model:OD8 3X16 model:OD15
What Does This Mean?
<http://www.hhoglabs.com/images/HHOGLabsSRS.pdf>